



L-VIT 1000 – the rugged, ultra-compact high speed camera

Hi-G-rated for 150+ G, Full HD @ 1000 fps, ready to be used in the most severe environments. A robust high resolution camera for demanding applications in research and development.

The L-VIT 1000 is particularly suited for all applications where a compact, portable, high resolution and robust camera is essential. The highly light-sensitive sensor covers the most ambitious application. The L-VIT 1000 is designed and certified to withstand G-forces in excess of 150 G /11 msec (all axes) and spikes of up to 200 G. Offering a wide range of signals for external control or feedback on camera status during tests, the L-VIT 1000 is a genuine all-in-one camera.

To round it all up, the comprehensive Imaging Studio software allows easy piloting from PC, laptop or tablet PC.

Unique features and benefits

- **Superior image quality** – with 1920 x 1080 Full HD resolution at up to 1000 fps L-VIT 1000 delivers crisp clear images.
- **Ultra compact and all in one** – L-VIT 1000 is an ultra-compact camera ready to shoot in rugged environments.
- **Sensitivity** – very light sensitive sensor.
- **Extensions** – Extensions such as CFast card or HDMI output on camera are available.

L-VIT 1000 – Key Specifications

Typical frame rates vs resolution

1920	1080	1000 fps
1920	720	1500 fps
1920	540	2000 fps
1920	256	4000 fps

Table shows typical resolution vs. fps, Resolution is freely adjustable within limitations of camera/sensor

Recording time

Memory Size	2 GB	4 GB	8 GB	16 GB
1920 x1080 @1000 fps	0.9 sec	1.8 sec	3.6 sec	7.2 sec

Optical/Sensor specifications

Image Sensor	CMOS Sensor
Pixel Size	10 micron
Light Sensitivity	ISO 8000 (monochrome), ISO 3600 (color)
Dynamic Range	Adjustable 8/10 Bit
Shutter Type	Global, independent of frame rate
Exposure Time	Free adjustable from 2 µsec to 1 / framing rate by software
Lens Mount	C-Mount or optional F-Mount

Camera and control features

Image Memory	2 GB standard up to 16 GB optional
Nonvolatile Memory	Optional CFast card interface. Camera can save image data on flash disk w/o PC attached
Power	10–36 VDC / 25–30 Watts depending on options and extensions
I/O Tolerance	TTL level, all I/O are 0–24 V tolerant
LED Control	LEDs on back and front indicates camera status
Reset	Reset function to reset camera status w/o affecting image memory
Power On/Off	Switch on/off, Remote Switch on
Battery	Refer to system configuration and optional extensions
Trigger Delay	Programmable up to 65 sec
Trigger Windowing/De-bouncing	User programmable trigger window to eliminate false triggering by external devices
Trigger Modes, Positions	Pre-post recording, freely adjustable in steps of 1 frame of total camera memory
Timing	High precision time base, temperature compensated
Multi-Buffer	Split buffer for up to 100 individual buffers
Auto-Download	Auto download to PC for 24/7 recording or automatic download to optional CFast card
Pre-Program of Camera	L-VIT 1000 may be pre-programmed with a specific set of commands. Ideal when camera can no longer be accessed before test and switch on is possible only by remote switch on
OSD	Information on camera, recording features, time stamp, and event marker may be added in image data. Position of OSD is set by user

Imaging studio features

Imaging Studio	Software suite to parameterize and control camera, handle data download and conversion of native files into most common single images and movie formats. Runs on Win 7/10, 32/64 Bit
Parameterization	Set all camera parameters for recording by convenient and easy-to-use software interface supports graphical setting of resolution
Display	Display multiple cameras simultaneously
Editing	Play back, edit and save sequences after recording with few clicks
OSD (on screen display)	OSD with camera parameters
Overlay	Overlay of recorded image with user adjustable opacity
Point & Click	Easy point and click measurement and manual tracking features
Export	Export of AOS native file format to avi, mpeg, mpeg4, bmp, tif, png, jpg
Image Processing	Manual or automatic color correction and white balance functionality
Batch Converter	Convert native files to movie files using off-line batch conversion

Data interface

Data Interface	Gigabit Ethernet (10/100/1000) with lockable RJ45 connector Option: 18 pin LEMO connector with all signals
I/O Interface	Solid 14 pin LEMO connector Option: 18 pin LEMO connector with all signals
Synchronization	Sync in / Sync out for phase-locked master-slave operation with other cameras or synchronization to external frequency
Armed Out	Armed out indicates camera is in recording mode and ready to receive trigger
Trigger In	Trigger input, rising, falling edge, TTL, switch closing/opening
Triggered Out	Indicates camera is triggered
Set_To_Rec	Used to set the camera from idle mode into recording
Remote Switch On	Switch on camera by simple 2 wire connection over a distance of up to 100 m (300 feet)
Event Marker	Event marker to record/mark events during image data acquisition
Strobe	Strobe out to synchronize external equipment to camera. Pulse width represents shutter time
IRIG-B	IRIG-B 122 input

Physical specifications

Size & Weight	width: 75 mm / height: 75 mm / length: 75 mm / 910 gr width: 2.95" / height: 2.95" / length: 2.95" / 1.4 lb
Operating Temperature	-10 ... +45 °C / +14 ... +113 °F
Storage Temperature	-40 ... +70 °C / -40 ... +158 °F
Shock Resistance	150 G / 11 msec all axis, spikes up to 200 G according EN 60068-2-27:2009
I/O Connector	LEMO type ref. FGG.2B.314.CLAD72Z (cable type)
CE	In compliance with relevant standards
Mounting	¼" UNC thread, bottom / M6 mounting threads on 4 sides

System configuration and optional extensions

Model/Extension	L-VIT 1000	L-VIT 1000 with 10 min battery	L-VIT 1000 with 10 min battery and CFast / HDMI output
Battery time	No backup battery	10 min	10 min
Size	75 x 75 x 75 mm	75 x 75 x 107 mm	75 x 75 x 124 mm

Your local AOS partner:



L-VIT 2500

High Speed Camera



Imaging for smart decisions...

Record when it happens!
Never be too late!



Superior image quality

1920 x 1080 Full HD resolution at up to 2500 fps L-VIT delivers crisp clear images.



Non volatile 64GB flash memory

Imminent backup of recording data to flash memory.
Never lose image data.



Built-in g-shock sensor

Built in g-sensor for direct in camera triggering.
Levels adjustable by software




Extensions

Extensions such as CFast Flash Disk or HDMI output on camera are available.

L-VIT 2500 - the rugged, ultra-compact high speed camera

- **Hi-G-rated for up to 200g, Full HD @ 2500 fps, ready to be used in the most severe environments.**
- **A robust high resolution camera for demanding applications in research and development.**

The L-VIT is particularly suited for all applications where a compact, portable, high resolution and robust camera is essential. The highly light-sensitive sensor covers the most ambitious application. The L-VIT is designed and certified to withstand G-forces in excess of 150g/10ms all axes and spikes of up to 200g without CFast option. Offering a wide range of signals for external control or feedback on camera status during tests, the L-VIT is a genuine all-in-one camera. Built-in non volatile 64GB flash memory automatically saves a copy of each live recording for data redundancy, this is crucial for critical tests that cannot be repeated. To round it all up, the comprehensive Imaging Studio software allows easy piloting from PC, laptop or tablet PC.



AOS Technologies AG

Taefernstrasse 20 | CH-5405 Baden-Daettwil

Tel. +41 (0)56 483 34 88

@AOSHIGHSPEEDCAM

info@aostechnologies.com

www.aostechnologies.com

L-VIT 2500 | Key Specifications

Typical frame rates vs resolution

1920	1080	2500 fps
1920	800	3360 fps
1920	720	3740 fps
1920	536	5000 fps
1920	260	10'100 fps

Maximum speed 195'600 fps, within limitations of sensor

Recording time

Memory Size	4 GB	8 GB	16 GB
1920 x1080 @ 1000 fps	2 sec	4 sec	8 sec

Optical/Sensor specifications

Image Sensor	CMOS sensor
Pixel Size	10 microns
Sensor Format	4/3" 19.20 x 10.80 mm
Light Sensitivity	ISO 8000 (monochrome), ISO 6000 (color) without gain
Gain	3 gain settings available, adjustable by software
Dynamic Range	Mono 10 Bit / Color 30 Bit
Shutter Type	Global, independent of frame rate
Exposure Time	Free adjustable from 1 µsec to 1 / framing rate by software
Lens Mount	C-Mount or optional EF/ F-Mount

Software and camera operation

Live Video	Live video out via Ethernet or when installed HDMI
Buffer Type	Circular buffer, parametrized by software
Number of Buffers	Up to 100 buffers, individually configurable by software
Trigger Modes	Pre-post recording, adjustable in steps of 1 frame, rising falling edge, delayed trigger, trigger debouncing Shock trigger (high g trigger)
Auto Exposure	Auto exposure for automatic brightness control
Auto Download	Auto download to PC or CFast card (CFast card optional)
Flash Backup	Automatic store of video data after trigger to flash memory.
Export Formats	Export in all popular movie and single image formats supported
Control SW	AOS Imaging Studio v4 for parametrization, recording, editing and exporting/converting of recordings included

Data interface

Data	Gigabit Ethernet RJ45 lockable
I/O	Solid 14 pin LEMO connector, compatible with all AOS camera series
I/O Tolerance	TTL compatible I/O, up to 24 V tolerant
Trigger In	Input for start stop recording, falling edge, switch closure
Armed Out	Armed out to indicate camera status ready for recording
Triggered Out	Indicates that trigger is received and camera finishes recording
Remote On	For remote switch on of camera
Sync In/Out	Sync in/out on camera
Strobe	Strobe out for synchronization of LED illumination
IRIG-B	IRIG-B 122 input for frame synchronisation and time stamping
Power Requirements	10...36 V /30 Watts
Analog inputs	Two analog inputs for recording status signals synchronized to recording

Your local AOS partner:

Options and add-on

Camera Memory	4 GB, 8 GB or 16 GB
Battery	Rechargeable battery for up to 12 mins operation lasting long enough to dump 16GB data to flash memory when power is not available
Video Out	HDMI video out on camera
Non-volatile Memory	Removable CFast interface with auto download functionality
ChillBox	For longer offboard use without passive cooling via metal surface use the camera mounted in the ChillBox
C-F-Mount Adapter	For F-Mount lenses, with dial for F-stop
C-EF-Mount Adapter	For EF-Mount lenses, remote control of Focus and aperture
Single Connector Interface	Single push-pull interface according German «Arbeitskreis»

Physical specifications

Size & Weight	width: 75 mm / height: 75 mm / length: 75 mm / 910 gr width: 2.95" / height: 2.95" / length: 2.95" / 1.4 lb
Operating Temperature	-10 ... +45 °C / +14 ... +113 °F
Storage Temperature	-40 ... +70 °C / -40 ... +158 °F
Shock Resistance	200g / 11msec all axis for configuration without CFast interface 150g / 11msec all axis, spikes up to 200g according EN 60068-2-27:2009 with CFast interface
I/O Connector	LEMO type ref. FGG.2B.314.CLAD72Z (cable type)
CE	In compliance with relevant standards
Mounting	¼" UNC thread, bottom / M6 mounting threads on 4 sides

System configuration and optional extensions

Model/Extension	L-VIT 2500	L-VIT 2500 with battery	L-VIT 2500 with CFast/HDMI output
Battery Time	No backup battery	12 min	12 min
Size	75 x 75 x 75 mm	75 x 75 x 107 mm	75 x 75 x 124 mm



Please check technical camera manual for detailed information



Specifications are subject to change without prior notice – v01.2022